

## OPEN SERVICE BODY

*Lower risks. Reduce Costs. Improve productivity.*

Keep productivity high and lower the risk of injuries and worker compensation claims by installing the right roof-storage solution on your utility vehicle.

Prime Design's ergonomic, patented and award-winning solutions have helped business owners around the world eliminate or reduce the costs, stress and business pressures caused by work-related injuries.



**PRR-0005**  
(model shown)

The only ergonomic ladder racks  
for service bodies  
(see back page)



Easy to use – deploys  
with only 2 fingers.



Control ladder deployment with  
adjustable hydraulic cylinder



Eliminates slip and fall hazards from  
climbing on bumper or tire.



Deter theft and secure contents  
with padlock ready handle



Improve productivity – Deploy  
or stow in less than 20 seconds.




Winner of ergonomic awards in USA,  
France, Germany and Australia.



Search terms "Open  
Service Body +  
ErgoRack" to find  
more information.


# OPEN SERVICE BODY

**UXV-211** *Curbside*  
**UVX-211** *Streetside*




**Specs:**  
Utility Vertical, Side Wall Mount,  
**Left hand:** UXV-211 /  
**Right hand:** UVX-211  
Folding attached handle  
**Weight:** 40 lbs  
**Crossbar Spacing:** 6, 7, 8 feet  
**Mounting surface width (B):** 7"  
**Body Width (A):** N/A  
**Mounting surface Length:** 64-100"

**UXV-201** *Curbside*  
**UVX-201** *Streetside*




**Specs:**  
Utility Vertical, Top Mount  
**Left hand:** UXV-201 /  
**Right hand:** UVX-201  
Folding attached handle  
**Weight:** 38 lbs  
**Crossbar Spacing:** 6, 7, 8 feet  
**Mounting surface width (B):** 12.25"  
**Body Width (A):** N/A  
**Mounting surface Length:** 76-100"

**UXV-203** *Curbside*  
**UVX-203** *Streetside*




**Specs:**  
Utility Vertical, Top Mount  
**Left hand:** UXV-203 /  
**Right hand:** UVX-203  
Hex drive with removable ratchet handle  
**Weight:** 41 lbs  
**Crossbar Spacing:** 6, 7, 8 feet  
**Mounting surface width (B):** 12.25"  
**Body Width (A):** N/A  
**Mounting surface Length:** 76-100"

**UXR-001-E** *Curbside*  
**URX-001-E** *Streetside*




**Specs:**  
Elevated Utility, Rotation  
**Left hand:** URX-001-E /  
**Right hand:** UXR-001-E  
With Chair Top Mount  
**Weight:** 48 lbs  
**Crossbar Spacing:** 5, 6, 7, 8 feet  
**Mounting surface width (B):** 13"  
**Body Width (A):** N/A  
**Mounting surface Length:** 64-100"

**UXR-002-E** *Curbside*  
**URX-002-E** *Streetside*



**Specs:**  
Elevated Utility, Rotation w/short handle  
**Left hand:** URX-002-E /  
**Right hand:** UXR-002-E  
With Chair Top Mount  
**Weight:** 48 lbs  
**Crossbar Spacing:** 5, 6, 7, 8 feet  
**Mounting surface width (B):** 10.5"  
**Body Width (A):** N/A  
**Mounting surface Length:** 64-100"

**UXR-003-E** *Curbside*



**Specs:**  
Elevated Utility, Rotation w/short handle  
**Right hand:** UXR-003-E  
With Chair Top Mount  
**Weight:** 46 lbs  
**Crossbar Spacing:** 6, 7, 8 feet  
**Mounting surface width (B):** 10.5"  
**Body Width (A):** N/A  
**Mounting surface Length:** 76-100"

**PRR-0005**




**Specs:**  
Elevated Utility, Rotation/Rotation,  
Two Crossbars, 76" - US Gen 4,  
RAC 1175/1176 Auto Clamp System  
With Elevated Top Mount  
**Weight:** 104 lbs  
**Crossbar Spacing:** 6, 7, 8 feet  
**Mounting surface width (B):** 13"  
**Body Width (A):** up to 74"  
**Mounting surface Length:** 76-100"

**PCR-0005**



**Specs:**  
Elevated Utility, Clamp/Rotation,  
Two Crossbars, 76" - US Gen 4,  
RAC 1175/1176 Auto Clamp System  
With Elevated Top Mount  
**Weight:** 100 lbs  
**Crossbar Spacing:** 7 feet  
**Mounting surface width (B):** 13"  
**Body Width (A):** up to 74"  
**Mounting surface Length:** 88"



Dimensions for your specific body model are critical to select the correct rack model. Use diagram to help determine which rack is right for your open utility body.